



# Best TOOLS for CUTTERS



# Thread: ISS IMS-Special thread

For your Sewer Rehab Robots:

IMS MIDI 4 large motor / DRIVEplus large motor





# THREAD: ISS IMS-Special thread

# IMS MIDI 4 large motor/ DRIVEplus large motor

Milling tools suitable for CIPP, PVC and ROOTS



### Diamond cone milling tool

Field of application: Opening of laterals and inlet lines

| Ømm   | Height mm | Segments | IMS-No.    | Code-No.     |
|-------|-----------|----------|------------|--------------|
| 40/20 | 47        | 16       | 015 01 241 | 21 49 40 160 |

Kardiam-BLACK-POWERLINE® Not for steel-reinforced concrete!



### Diamond globe milling tool

Field of application: Opening of laterals and inlet lines

| Ømm | Height mm | Segments  | IMS-No.    | Code-No.     |
|-----|-----------|-----------|------------|--------------|
| 42  | 45        | 28 double | 015 01 243 | 21 49 40 162 |

Kardiam-BLACK-POWERLINE® Not for steel-reinforced concrete!



### Diamond globe milling tool - transparent -

Field of application: Opening of laterals and inlet lines

| Ømm | Height mm | Segments     | IMS-No.    | Code-No.     |
|-----|-----------|--------------|------------|--------------|
| 42  | 45        | 14 - 4 wings | 015 01 203 | 21 49 40 345 |

Kardiam-BLACK-POWERLINE® Not for steel-reinforced concrete!



### Diamond globe milling tool - transparent -

Field of application: Opening of laterals and inlet lines

| Ømm | Height mm | Segments     | IMS-No.    | Code-No.     |
|-----|-----------|--------------|------------|--------------|
| 50  | 57        | 30 - 6 wings | 015 01 213 | 21 49 40 351 |

Kardiam-BLACK-POWERLINE® Not for steel-reinforced concrete!



### Diamond globe milling tool - transparent -

Field of application: Opening of laterals and inlet lines

| Ømm | Height mm | Segments     | IMS-No.    | Code-No.     |
|-----|-----------|--------------|------------|--------------|
| 56  | 40        | 33 - 6 wings | 015 01 242 | 21 49 40 161 |

Kardiam-BLACK-POWERLINE® Not for steel-reinforced concrete!







### Diamond plate milling tool

Field of application: Opening of laterals and inlet lines, removes deposits

| Ømm | Height mm | Segments | IMS-No.    | Code-No.     |
|-----|-----------|----------|------------|--------------|
| 63  | 27        | 24       | 015 01 215 | 21 49 40 165 |

Kardiam-BLACK-POWERLINE® Not for steel-reinforced concrete!



### Carbide granulate globe milling tool

Field of application: Opening of laterals and inlet lines, removes deposits

| Ømm | Height mm | Grain size | IMS-No.    | Code-No.     |
|-----|-----------|------------|------------|--------------|
| 55  | 50        | 2,5/3,0    | 015 01 212 | 21 45 00 185 |

### Milling tools suitable for CONCRETE, VITRIFIED CLAY and DEPOSITS



### Diamond globe milling tool

Field of application: Preparatory milling of laterals, Removal of intruding laterals and deposits

| Ømm | Height mm | Segments | IMS-No.    | Code-No.     |
|-----|-----------|----------|------------|--------------|
| 48  | 47        | 21       | 015 01 202 | 21 49 70 109 |



### Diamond globe milling tool

Field of application: Preparatory milling of laterals, Removal of intruding laterals and deposits

| Ømm | Height mm | Segments | IMS-No.    | Code-No.     |
|-----|-----------|----------|------------|--------------|
| 60  | 64        | 16       | 015 01 201 | 21 49 70 079 |



### Diamond halfglobe milling tool

Field of application: Preparatory milling of laterals, Removal of intruding laterals and deposits

| Ømm | Height mm | Segments | IMS-No.    | Code-No.     |
|-----|-----------|----------|------------|--------------|
| 65  | 30        | 10       | 015 01 244 | 21 49 60 095 |





## THREAD: ISS IMS-Special thread

# IMS MIDI 4 large motor/ DRIVEplus large motor

Milling tools suitable for CONCRETE, VITRIFIED CLAY and DEPOSITS



### Diamond cone milling tool

Field of application: Preparatory milling of laterals, removal of intruding laterals and deposits

| Ømm   | Height mm | Segments | IMS-No.    | Code-No.     |
|-------|-----------|----------|------------|--------------|
| 38/28 | 52        | 6        | 015 01 210 | 21 49 60 079 |



### Diamond inflow pipe milling tool

Field of application: Preparatory milling of laterals, removal of intruding laterals and deposits

| Ømm | Height mm | Segments | IMS-No.    | Code-No.     |
|-----|-----------|----------|------------|--------------|
| 53  | 30        | 8 DN 100 | 015 01 211 | 21 49 60 082 |
| 85  | 33        | 12 DN250 | 015 01 200 | 21 49 60 080 |



Diamond inflow pipe milling tool - elastic/spring loaded -

Field of application: Preparatory milling of laterals, removal of intruding laterals and deposits

| Ømm | Height mm | Segments | IMS-No.    | Code-No.     |
|-----|-----------|----------|------------|--------------|
| 85  | 35        | 12 DN250 | 015 01 214 | 21 49 60 092 |



**Diamond mushroom shaped milling tool** - elastic/spring loaded - Field of application: Preparatory milling of laterals, removal of intruding laterals and deposits

| Ømm | Height mm | Segments | IMS-No.    | Code-No.     |
|-----|-----------|----------|------------|--------------|
| 80  | 38        | 12 DN200 | 015 01 216 | 21 49 70 178 |





# **ACCESSORIES - ISS IMS-Special thread**

# IMS MIDI 4 large motor/ DRIVEplus large motor



### **Corund grindstone**

Field of application: Grinding of metal and cast iron pipes, removal of intruding obstacles

| Ømm | Borehole /<br>Thread | Height<br>mm | IMS-No.    | Code-No.     |
|-----|----------------------|--------------|------------|--------------|
| 80  | ISS-IMS              | 30           | 015 01 207 | 21 50 00 133 |
| 80  | 22,2                 | 27           | 015 01 154 | 21 50 00 102 |



### Multifunctional key for changing the screw connection

(Corund grindstone Ø 80 + Ø 90 / 110):

| Total length<br>mm | SW | Pins | IMS-No.    | Code-No.     |
|--------------------|----|------|------------|--------------|
| 160                | 24 | 2    | 015 01 158 | 21 50 00 111 |



### **Extensions IMS-ISS-Special thread**

| Ømm | Useful length mm | IMS-No.    | Code-No.     |
|-----|------------------|------------|--------------|
| 24  | 30               | 015 01 209 | 21 50 00 132 |



### Adapter: IMS-ISS-Special thread to 5/8"UNC

| Ømm | Useful length mm | IMS-No.    | Code-No.     |
|-----|------------------|------------|--------------|
| 24  | 30               | 015 01 206 | 21 50 00 131 |



### Adapter: IMS-ISS-Special thread to IMS-Micro/...

| Ømm | Useful length mm | IMS-No.    | Code-No.     |
|-----|------------------|------------|--------------|
| 24  | 39               | 015 01 240 | 21 50 00 246 |





# **ACCESSORIES - ISS IMS-Special thread**

# IMS MIDI 4 large motor/ DRIVEplus large motor



### **Brushes**

Field of application: Post-processing of inliner openings, removal of residual film, Cleaning, roughening work, ...

| Brushes   | Ømm | Height | IMS-No.    | Code-No.     |
|-----------|-----|--------|------------|--------------|
|           |     | mm     |            |              |
| Cup brush | 65  | 50     | 015 01 234 | 21 50 00 213 |
| Cup brush | 80  | 70     | 015 01 204 | 21 50 00 214 |



### Round brush + Mounting

Field of application: Post-processing of inliner openings, removal of residual film, Cleaning, roughening work, ...

| Brushes                               | Ømm | Height<br>mm | IMS-No.    | Code-No.     |
|---------------------------------------|-----|--------------|------------|--------------|
|                                       |     |              |            |              |
| Round brush                           | 80  | 18           | 015 01 227 | 21 50 00 238 |
| Mounting for round<br>brush Ø80mm H18 | 30  | 42           | 015 01 220 | 21 50 00 242 |
| Round brush                           | 80  | 25           | 015 01 228 | 21 50 00 239 |
| Mounting for round<br>brush Ø80mm H25 | 30  | 49           | 015 01 221 | 21 50 00 243 |




### Grinding wheel mounting IMS-ISS-Special thread to ø22,2

| Ømm | Useful length mm | IMS-No.    | Code-No.     |
|-----|------------------|------------|--------------|
| 45  | 34               | 015 01 239 | 21 50 00 247 |



info@ims-robotics.de

ims-robotics.de



in cooperation with



Best TOOLS for CUTTERS

Phone: +49 (0)7520-9515-0

info@kardiam.de

www.kardiam.de

+49 (0)7520-9515-29